

PrimaVision Mini for CDM

HID-PV m 35 /I CDM 220-240V 50/60Hz

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design


Product data

| Operating and Electrical | |
|--|---------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Input frequency | 50 to 60 Hz |
| Earth leakage current (max.) | 0.5 mA |
| Inrush current width | 0.25 ms |
| Inrush current peak (max.) | 15 A |
| Number of products on MCB (16 A type B) (nom.) | 24 |
| Wiring | |
| Cable length from device to lamp | 2 m |
| Connector type | Insert |
| Temperature | |
| Ambient temperature range | -20°C to 45°C |
| T-case lifetime (nom.) | 85 °C |
| T-Case maximum (max.) | 85 °C |
| Mechanical and Housing | |
| Housing | Independent |

| Approval and Application | |
|-----------------------------------|--|
| Approval marks | F-Marking CE marking ENEC certificate CB certificate |
| Product Data | |
| Order product name | HID-PV m 35/I CDM 220-240V 50/60Hz |
| Full product name | HID-PV m 35 /I CDM 220-240V 50/60Hz |
| Full EOC | 872790089164500 |
| Order code | 89164500 |
| Material no. (12 NC) | 913700653566 |
| Local order code | PVM35I |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8711500881724 |
| Numerator – packs per outer box | 10 |
| EAN/UPC - Case | 8727900891645 |

PrimaVision Mini for CDM

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | A3 | B1 |
|---------------------------------------|--------|---------|----------|----------|----------|---------|
| HID-PV m 35/I CDM 220-240V 50/60Hz | 4.8 mm | 34.0 mm | 234.7 mm | 225.1 mm | 202.0 mm | 49.4 mm |

