



PrimaVision for SDW-TG


HID-PV 100 /S SDW-TG 220-240V 50/60Hz

Robust, lightweight and one-piece HID electronic gear for SDW-TG lamps (mini White SON) Lightweight, one-piece electronic gear for 50 and 100 W SDW-TG lamps (mini White SON)

Product data

Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing	/S
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		
Inrush Current Width	0.50 ms		
Inrush Current Peak (Max)	33 A		
Number of Products on MCB (16A Type B) (Nom)	14		
Wiring		Approval and Application	
Cable Length From Device to Lamp	2 m	Approval Marks	CE marking ENEC certificate CB Certificate
Connector Type	Insert		
Temperature		Product Data	
Ambient temperature range	-20 °C to 60 °C	Order product name	HID-PV 100 /S SDW-TG 220-240V 50/60Hz
T-Case Lifetime (Nom)	75 °C	Full product name	HID-PV 100 /S SDW-TG 220-240V 50/60Hz
T-Case Maximum (Max)	85 °C	Full product code	872790088754900
		Order code	913700656566
		Material Nr. (12NC)	913700656566
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500881861
		Numerator - Packs per outer box	10
		EAN/UPC - Case	8727900887549

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV 100 /S SDW-TG 220-240V 50/60Hz	4.5 mm	37.0 mm	150.0 mm	133.6 mm	90.0 mm	70.0 mm

