



# HF-Performer Intelligent for TL5 HE/HO lamps

## HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V

Intelligent, flat, slim, lightweight high-frequency electronic ballast for TL5 fluorescent lamps

### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.5 mA
Inrush Current Width	0.4 ms
Inrush Current Peak (Max)	45 A
Number of Products on MCB (16A Type B) (Nom)	12

Wiring	
Connector Type Input Terminals	Insert
Connector Type Output Terminals	Insert
Cable Length From Device to Lamp	2 m

Temperature	
Ambient temperature range	-25 °C to 50 °C
T-Case Lifetime (Nom)	75 °C
T-Case Maximum (Max)	75 °C


Mechanical and Housing	
Housing	L360x30x22

Approval and Application	
Energy Efficiency Index	A2 BAT
Safety Standard	IEC 61347-2-3
Environmental Standard	ISO 14001
Approval Marks	CE marking ENEC certificate VDE-EMV certificate

Product Data	
Order product name	HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V
Full product name	HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V
Full product code	872790088775400
Order code	88775400
Material Nr. (12NC)	913700657666
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500881960
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900887754

# HF-Performer Intelligent for TL5 HE/HO lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V	4.2 mm	22 mm	360 mm	350 mm	30 mm

