



# HID-GreenVision GP-SON

## HID-GVIII 600W/P GP-SON 400V

Full electronic driver for GP-SON 600/1000W lamps

### Product data

#### Operating and Electrical

Input Voltage	400 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	1.6 ms
Inrush Current Peak (Max)	30 A

#### Wiring

Connector Type	JST VH Connector
----------------	------------------

#### Temperature

Ambient temperature range	0 °C to 40 °C
T-Case Lifetime (Nom)	70 °C

#### Controls and Dimming

Control Interface	None
-------------------	------

#### Mechanical and Housing

Housing	L 181x150x58
---------	--------------

#### Approval and Application

Energy Efficiency Index	A2
Surge Protection (Common/Differential)	EN61547 (L-L 2kV, L-G 4kV) kV
Safety Standard	EN60928, 60926
Environmental Standard	ISO 14001
Approval Marks	CE marking ENEC certificate CB Certificate KEMA Keur certificate

#### Product Data

Order product name	HID-GVIII 600W/P GP-SON 400V
Full product name	HID-GVIII 600W/P GP-SON 400V
Full product code	872790090902900
Order code	913700660366
Material Nr. (12NC)	913700660366
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500999481
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900909029

HID-GreenVision GP-SON

Dimensional drawing

Product	C1	A1	B1
HID-GVIII 600W/P GP-SON 400V	58 mm	181 mm	150 mm

