



PrimaVision Xtreme for CPO

HID-PV Xt 45 CPO C1 208-277V

Compact, robust, outdoor, one-piece, electronic ballasts for CosmoPolis White (CPO-TW) lamps

Product data


Operating and Electrical	
Input Voltage	208-240-277 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.7 mA
Inrush Current Width	0.24 ms
Input Current (Nom)	0.26 A
Inrush Current Peak (Max)	28 A
Number of Products on MCB (16A Type B) (Nom)	11
Wiring	
Cable Length From Device to Lamp	10 m
Connector Type	WAGO series 804
Temperature	
Ambient temperature range	-30 °C to 50 °C
T-Case Lifetime (Nom)	80 °C
Mechanical and Housing	
Housing	C1

Approval and Application	
Surge Protection (Common/Differential)	EN61547 (L-L 2kV, L-G 4kV), 10 kV TIL
Safety Standard	IEC 607, 609, 926, 928 [No Standard for HID Lamp drivers exists. Requirements in these standards to be used if considered relevant for the product.]
Environmental Standard	ISO 14001
Approval Marks	F-Marking CE marking ENEC certificate VDE-EMV certificate

Product Data	
Order product name	HID-PV Xt 45 CPO C1 208-277V
Full product name	HID-PV Xt 45 CPO C1 208-277V
Full product code	871829121204100
Order code	21204100
Material Nr. (12NC)	913700672966
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291212041
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291212058

PrimaVision Xtreme for CPO

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV Xt 45 CPO C1 208-277V	5.0 mm	65.0 mm	150.0 mm	135.9 mm	65.0 mm	46.8 mm

