



PrimaVision Xtreme for CPO

HID-PV Xt 45 CPO C1 208-277V

Highly reliable electronic drivers for CPO lamps; designed to save energy by offering better light efficiency than magnetic drivers and to reduce maintenance costs thanks to 80,000-hour lifetime and integrated lightning protection

Product data

Operating and Electrical	
Input Voltage	208-240-277 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Earth leakage current (max.)	0.7 mA
Inrush current width	0.24 ms
Input current (nom.)	0.26 A
Inrush current peak (max.)	28 A
Number of products on MCB (16 A type B) (nom.)	11
Wiring	
Cable length from device to lamp	10 m
Connector type	WAGO series 804
Temperature	
Ambient temperature range	-30 °C to 50 °C
T-case lifetime (nom.)	80 °C


Mechanical and Housing	
Housing	C1
Approval and Application	
Surge Protection (Common/Differential)	EN61547 (L-L 2 kV, L-G 4 kV), 10 kV TIL
Safety standard	IEC 607, 609, 926, 928 [No Standard for HID Lamp drivers exists. Requirements in these standards to be used if considered relevant for the product.]
Environmental standard	ISO 14001
Approval marks	F-Marking CE marking ENEC certificate VDE-EMV certificate

Product Data	
Order product name	HID-PV Xt 45 CPO C1 208-277V
Full product name	HID-PV Xt 45 CPO C1 208-277V
Full EOC	871829121204100
Order code	21204100
Material no. (12 NC)	913700672966
Local order code	PVXT45CPOC
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291212041

PrimaVision Xtreme for CPO

Numerator – packs per outer box	12
EAN/UPC – Case	8718291212058

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV Xt 45 CPO C1 208-277V	5.0 mm	65.0 mm	150.0 mm	135.9 mm	65.0 mm	46.8 mm

