



DynaVision Programmable Xtreme for SON

HID-DV PROG Xt 70 SON C1 208-277V

Highly reliable and flexible electronic drivers for SON lamps; designed to save energy via integrated controls, and to reduce maintenance costs thanks to 80,000-hour lifetime and integrated lightning protection. The DynaVision Programmable product family is the perfect basis for any sort of lighting management solution.

Produktdata

Drift og elektronikk	
Inngangsspenning	208-240-277 V
Line Frequency	50 to 60 Hz
Inngangsfrekvens	50 til 60 Hz
Jordlekkasjestrøm (maks.)	0,7 mA
Startstrøm-bredde	0,24 ms
Inngangsstrøm (nom.)	0.39 A
Startstrøm-topp (maks.)	28 A
Antall produkter på MCB (16A type B) (nom.)	11
Kabling	
Kabellengde fra enhet til lyskilde	10 m
Tilkoblingstype	WAGO-serien 804
Temperatur	
Omgivelsestemperatur	-30 °C til 50 °C


Temperatur for optimal levetid for forkoblingsinnfatningen (nom.)	80 °C
Kontroller og dimming	
Kontrollgrensesnitt	PROG
Mekanikk og innfatning	
Armaturhus	C1
Godkjenning og bruksområde	
Surge Protection (Common/Differential)	EN61547 (L-L 2 kV, L-G 4 kV), 10 kV TIL
Sikkerhetsstandard	IEC 607, 609, 926, 928 [Det finnes ingen standard for HID-lampedrivere. Krav i disse standardene skal brukes hvis de anses som relevante for produktet.]
Miljøstandard	ISO 14001

DynaVision Programmable Xtreme for SON

Godkjenningsmerker	F-merking CE-merking VDE-EMV-sertifikat ENEC-sertifikat
Produktdata	
Produktnavn for bestilling	HID-DV PROG Xt 70 SON C1 208-277V
Fullstendig produktnavn	HID-DV PROG Xt 70 SON C1 208-277V
Full EOC	871829121222500
Lokal kodebeskrivelse	3381872
Bestillingskode	21222500

Materialenr. (12NC)	913700678666
Lokal bestillingskode	3381872
SAP-teller – antall per pakke	1
EAN/UPC – produkt/boks	8718291212225
SAP-teller – pakker per utvendige	12
EAN/UPC – boks	8718291212232

Målskisse



Product	D1	C1	A1	A2	B1	B2
HID-DV PROG Xt 70 SON C1 208-277V	5,0 mm	65,0 mm	150,0 mm	135,9 mm	65,0 mm	46,8 mm

