

# AspiraVision Compact for CDM

## HID-AV C 50 /I CDM 220-240V 50/60Hz

AspiraVision is the mark of excellence in HID electronic gear technology – high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps. The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver.

### Product data


Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.5 mA
Input Current (Nom)	0.26 A
Wiring	
Connector Type	WAGO series 804
Temperature	
Ambient temperature range	-20 °C to 55 °C
Controls and Dimming	
Control Interface	-
Mechanical and Housing	
Housing	/I

Approval and Application	
Surge Protection (Common/ Differential)	EN61547 (L-L 1kV, L-G 2kV) kV
Approval Marks	F-Marking CE marking ENEC certificate VDE certificate VDE-EMC marking C-Tick certificate CERTCELMA

Product Data	
Order product name	HID-AV C 50 /I CDM 220-240V 50/60Hz
Full product name	HID-AV C 50 /I CDM 220-240V 50/60Hz
Full product code	871829119385200
Order code	913700680566
Material Nr. (12NC)	913700680566
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291193852
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291193869

# AspiraVision Compact for CDM

## Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-AV C 50 /I CDM 220-240V 50/60Hz	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm

