



PrimaVision Mini for CDM

HID-PV C 35 /GMI CDM 220-240V 50/60Hz NG

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	0.33 ms
Inrush Current Peak (Max)	33 A
Number of Products on MCB (16A Type B) (Nom)	24
Wiring	
Cable Length From Device to Lamp	2 m
Connector Type	Insert
Temperature	
Ambient temperature range	-20 °C to 50 °C
T-Case Lifetime (Nom)	75 °C
T-Case Maximum (Max)	75 °C
Mechanical and Housing	
Housing	/GMI

Approval and Application	
Approval Marks	F-Marking CE marking ENEC certificate VDE-EMV certificate CB Certificate
Product Data	
Full product code	871829120225700
Order product name	HID-PV C 35 /GMI CDM 220-240V 50/60Hz NG
Order code	913700681195
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913700681195
Full product name	HID-PV C 35 /GMI CDM 220-240V 50/60Hz NG
EAN/UPC - Case	8718291202264
EAN/UPC - Product/Case	8718291202257

PrimaVision Mini for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV C 35 /GMI CDM 220-240V 50/60Hz NG	4.8 mm	34.5 mm	188 mm	170 mm	62.7 mm

