



PrimaVision Economy for CDM lamps

HID-PV E 50 /S CDM 220-240V


Single CDM lamp operation, single HID electronic gear – improves cost effectiveness and increases luminaire design flexibility

Product data

Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing	/S
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz	Approval and Application	
Inrush Current Width	0.25 ms	Approval Marks	CE marking ENEC certificate VDE certificate
Inrush Current Peak (Max)	26 A		
Number of Products on MCB (16A Type B) (Nom)	24	Product Data	
		Full product code	871829121296600
Wiring		Order product name	HID-PV E 50 /S CDM 220-240V
Cable Length From Device to Lamp	2 m	Order code	913700684266
Connector Type	Insert	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	12
Temperature		Material Nr. (12NC)	913700684266
Ambient temperature range	-20 °C to 50 °C	Full product name	HID-PV E 50 /S CDM 220-240V
T-Case Lifetime (Nom)	80 °C	EAN/UPC - Case	8718291212973
T-Case Maximum (Max)	80 °C	EAN/UPC - Product/Case	8718291212966

PrimaVision Economy for CDM lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV E 50 /S CDM 220-240V	4.9 mm	32.2 mm	109.6 mm	98.5 mm	74.4 mm	63.7 mm

