



DynaVision Programmable Xtreme for CPO

HID-DV PROG Xt 140 CPO L1 208-277V

Highly reliable and flexible electronic drivers for CPO lamps; designed to save on energy costs via integrated controls and to reduce maintenance costs thanks to 80,000-hour lifetime and integrated lightning protection. The DynaVision Programmable product family is the perfect basis for any sort of lighting management solution.

Produktdata


Drift og elektronikk		Temperatur	
Inngangsspenning	208-240-277 V	Omgivelsestemperatur	-30 °C til 55 °C
Line Frequency	50 to 60 Hz	Temperatur for optimal levetid for	80 °C
Inngangsfrekvens	50 til 60 Hz	forkoblingsinnfatningen (nom.)	
Strømfaktor 50 % belastning (min)	0,98		
Jordlekkasjestrøm (maks.)	0,7 mA		
Startstrøm-bredde	0,47 ms		
Inngangsstrøm (nom.)	0.75 A		
Startstrøm-topp (maks.)	52 A		
Antall produkter på MCB (16A type B) (nom.)	5		
Kabling		Kontroller og dimming	
Kabellengde fra enhet til lyskilde	10 m	Kontrollgrensesnitt	PROG
Tilkoblingstype	WAGO-serien 804		
		Mekanikk og innfatning	
		Armaturhus	Q
		Godkjenning og bruksområde	
		Surge Protection (Common/Differential)	EN61547 (L-L 2 kV, L-G 4 kV), 10 kV TIL
		Sikkerhetsstandard	IEC 607, 609, 926, 928 [Det finnes ingen standard for HID-lampedrivere. Krav i disse standardene skal brukes hvis de anses som relevante for produktet.]

DynaVision Programmable Xtreme for CPO

Miljøstandard	ISO 14001
Godkjenningsmerker	F-merking CE-merking VDE-EMV-sertifikat CB-sertifikat ENEC-sertifikat
Produktdata	
Produktnavn for bestilling	HID-DV PROG Xt 140 CPO Q 208-277V
Fullstendig produktnavn	HID-DV PROG Xt 140 CPO L1 208-277V
Full EOC	871829124153900

Bestillingskode	24153900
Materialenr. (12NC)	913700685966
SAP-teller – antall per pakke	1
EAN/UPC – produkt/boks	8718291241539
SAP-teller – pakker per utvendige	12
EAN/UPC – boks	8718291241546

Målskisse



Product	D1	C1	A1	A2	B1	B2
HID-DV PROG Xt 140 CPO Q 208-277V	4,5 mm	40,0 mm	150,0 mm	133,6 mm	90,0 mm	70,0 mm

