

# PrimaVision Compact for CDM

## HID-PV C 20 /S CDM 220-240V 50/60Hz

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps


### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.25 mA
Inrush Current Width	0.30 ms
Inrush Current Peak (Max)	18.3 A
Number of Products on MCB (16A Type B) (Nom)	24
Wiring	
Cable Length From Device to Lamp	2 m
Connector Type	Push
Temperature	
Ambient temperature range	-20 °C to 60 °C
T-Case Lifetime (Nom)	80 °C
T-Case Maximum (Max)	80 °C
Mechanical and Housing	
Housing	/S

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Safety Standard	EN 61347-2-12
Environmental Standard	-
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	HID-PV C 20 /S CDM 220-240V 50/60Hz
Full product name	HID-PV C 20 /S CDM 220-240V 50/60Hz
Full product code	871829169400700
Order code	913700698566
Material Nr. (12NC)	913700698566
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291694007
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291694014

# PrimaVision Compact for CDM

## Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV C 20 /S CDM 220-240V 50/60Hz	4.5 mm	32.1 mm	110.0 mm	98.5 mm	75.0 mm	63.5 mm

