

# Gear for SDW-T lamps

## BSL 100 K202-A2-TS 230V 50Hz

CSLS electronic control unit with impregnated (HID 'BASIC' ) or encapsulated (HID 'Heavy Duty' ) electromagnetic ballasts

### Warnings and Safety



- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BSL 100 K202-A2-TS 230V 50Hz	
<b>Input Voltage</b>	230 V	<b>Full product code</b>		871869674076700	
<b>Line Frequency</b>	50 Hz	<b>Order code</b>		74076700	
<b>Input Frequency</b>	50 Hz	<b>Material Nr. (12NC)</b>		913700751826	
		<b>Numerator - Quantity Per Pack</b>		1	
		<b>EAN/UPC - Product/Case</b>		8718696740767	
		<b>Numerator - Packs per outer box</b>		6	
		<b>EAN/UPC - Case</b>		8718696740774	
<b>Approval and Application</b>					
<b>Approval Marks</b>	CE marking ENEC certificate				
<b>Product Data</b>					
<b>Order product name</b>	BSL 100 K202-A2-TS 230V 50Hz				

Gear for SDW-T lamps

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSL 100 K202-A2-TS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm

