

Gear for SDW-T lamps

BSL 100 K202-A2-TS 230V 50Hz

CSLS electronic control unit with impregnated (HID "BASIC") or encapsulated (HID "Heavy Duty") electromagnetic ballasts

Warnings and Safety

- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)


Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input frequency	50 Hz
Wiring	
Connector type	Screw
Approval and Application	
Approval marks	CE marking ENEC certificate
Product Data	
Order product name	BSL 100 K202-A2-TS 230V 50Hz

Full product name	BSL 100 K202-A2-TS 230V 50Hz
Full EOC	871869674076700
Order code	74076700
Material no. (12 NC)	913700751826
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696740767
Numerator – packs per outer box	6
EAN/UPC – Case	8718696740774

Gear for SDW-T lamps

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSL 100 K202-A2-TS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm

