

# HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

## BSN 70 K202-A2-TS-R 230V 50Hz



Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BSN 70 K202-A2-TS-R 230V 50Hz	
Input Voltage	230 V	<b>Full EOC</b>		871869674084200	
Line Frequency	50 Hz	<b>Order code</b>		74084200	
Input frequency	50 Hz	<b>Material no. (12 NC)</b>		913700752226	
		<b>SAP numerator – quantity per pack</b>		1	
<b>Wiring</b>		<b>EAN/UPC — Product/Case</b>		8718696740842	
Connector type	Screw	<b>Numerator – packs per outer box</b>		6	
		<b>EAN/UPC - Case</b>		8718696740859	
<b>Approval and Application</b>					
Approval marks	CE marking ENEC certificate				
<b>Product Data</b>					
Order product name	BSN 70 K202-A2-TS-R 230V 50Hz				

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 70 K202-A2-TS-R 230V 50Hz	118 mm	94 mm	61 mm	52 mm	6.2 mm

