



# HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

## BSN 100 L33-A2-TS 230V 50Hz

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BSN 100 L33-A2-TS 230V 50Hz	
Input Voltage	230 V	<b>Full EOC</b>		871869674094100	
Line Frequency	50 Hz	<b>Order code</b>		74094100	
Input frequency	50 Hz	<b>Material no. (12 NC)</b>		913700752526	
		<b>SAP numerator – quantity per pack</b>		1	
		<b>EAN/UPC — Product/Case</b>		8718696740941	
		<b>Numerator – packs per outer box</b>		6	
		<b>EAN/UPC - Case</b>		8718696740958	
<b>Approval and Application</b>					
<b>Approval marks</b>		CE marking ENEC certificate			
<b>Product Data</b>					
<b>Order product name</b>		BSN 100 L33-A2-TS 230V 50Hz			

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 100 L33-A2-TS 230V 50Hz	123 mm	108 mm	65 mm	53 mm	6.2 mm

