

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 100 L33-A2-TS 230V 50Hz


Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

| | | | | | |
|---------------------------------|-----------------------------|--|--|-----------------------------|--|
| Operating and Electrical | | Full product name | | BSN 100 L33-A2-TS 230V 50Hz | |
| Input Voltage | 230 V | Full product code | | 871869674094100 | |
| Line Frequency | 50 Hz | Order code | | 913700752526 | |
| Input Frequency | 50 Hz | Material Nr. (12NC) | | 913700752526 | |
| | | Numerator - Quantity Per Pack | | 1 | |
| | | EAN/UPC - Product/Case | | 8718696740941 | |
| | | Numerator - Packs per outer box | | 6 | |
| | | EAN/UPC - Case | | 8718696740958 | |
| | | | | | |
| Wiring | | | | | |
| Connector Type | Screw | | | | |
| | | | | | |
| Approval and Application | | | | | |
| Approval Marks | CE marking ENEC certificate | | | | |
| | | | | | |
| Product Data | | | | | |
| Order product name | BSN 100 L33-A2-TS 230V 50Hz | | | | |

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



| Product | A1 | A2 | B1 | C1 | D1 |
|-----------------------------|--------|--------|-------|-------|--------|
| BSN 100 L33-A2-TS 230V 50Hz | 123 mm | 108 mm | 65 mm | 53 mm | 6.2 mm |

