

# HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

## BSN 150 L33-A2-TS 230V 50Hz

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps



### Product data

<b>Operating and Electrical</b>	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
<b>Wiring</b>	
Connector Type	Screw
<b>Approval and Application</b>	
Approval Marks	CE marking ENEC certificate
<b>Product Data</b>	
Order product name	BSN 150 L33-A2-TS 230V 50Hz

Full product name	BSN 150 L33-A2-TS 230V 50Hz
Full product code	871869674100900
Order code	913700752826
Material Nr. (12NC)	913700752826
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696741009
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696741016

# HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

## Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 150 L33-A2-TS 230V 50Hz	126 mm	108 mm	81 mm	66 mm	6.2 mm

