



HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 250 K202-A2-TS-R 230V 50Hz


Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name		BSN 250 K202-A2-TS-R 230V 50Hz	
Input Voltage	230 V	Full EOC		871869674104700	
Line Frequency	50 Hz	Order code		74104700	
Input frequency	50 Hz	Material no. (12 NC)		913700753026	
		SAP numerator – quantity per pack		1	
		EAN/UPC — Product/Case		8718696741047	
		Numerator – packs per outer box		6	
		EAN/UPC - Case		8718696741054	
Approval and Application					
Approval marks	CE marking ENEC certificate				
Product Data					
Order product name	BSN 250 K202-A2-TS-R 230V 50Hz				

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 250 K202-A2-TS-R 230V 50Hz	160 mm	139 mm	76 mm	65 mm	6.2 mm

