

HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

BSN 100/70 K302-A2-TS 230V 50Hz



Impregnated electromagnetic copper/iron double-wattage ballasts for use with an external series (superimposed) ignitor for CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name	
Input Voltage	230 V	Full EOC	871869674112200
Line Frequency	50 Hz	Order code	74112200
Input frequency	50 Hz	Material no. (12 NC)	913700753326
Wiring		SAP numerator – quantity per pack	1
Connector type	Screw	EAN/UPC – Product/Case	8718696741122
Approval and Application		Numerator – packs per outer box	6
Approval marks	CE marking ENEC certificate	EAN/UPC – Case	8718696741139
Product Data			
Order product name	BSN 100/70 K302-A2-TS 230V 50Hz		

HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 100/70 K302-A2-TS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm

