

# HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

## BSN 100/70 K302-A2-TS 230V 50Hz



Impregnated electromagnetic copper/iron double-wattage ballasts for use with an external series (superimposed) ignitor for CDO, MH, HPI (Plus) and SON lamps

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BSN 100/70 K302-A2-TS 230V 50Hz	
Input Voltage	230 V	<b>Full product code</b>		871869674112200	
Line Frequency	50 Hz	<b>Order code</b>		913700753326	
Input Frequency	50 Hz	<b>Material Nr. (12NC)</b>		913700753326	
		<b>Numerator - Quantity Per Pack</b>		1	
		<b>EAN/UPC - Product/Case</b>		8718696741122	
		<b>Numerator - Packs per outer box</b>		6	
		<b>EAN/UPC - Case</b>		8718696741139	
<b>Approval and Application</b>					
Approval Marks		CE marking ENEC certificate			
<b>Product Data</b>					
Order product name		BSN 100/70 K302-A2-TS 230V 50Hz			

HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 100/70 K302-A2-TS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm

