



HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

BSN 150/100 K302-A2-TS 230V 50Hz



Impregnated electromagnetic copper/iron double-wattage ballasts for use with an external series (superimposed) ignitor for CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name		BSN 150/100 K302-A2-TS 230V 50Hz	
Input Voltage	230 V	Full EOC		871869674114600	
Line Frequency	50 Hz	Order code		74114600	
Input frequency	50 Hz	Material no. (12 NC)		913700753426	
		SAP numerator – quantity per pack		1	
Wiring		EAN/UPC — Product/Case		8718696741146	
Connector type	Screw	Numerator – packs per outer box		6	
		EAN/UPC - Case		8718696741153	
Approval and Application					
Approval marks	CE marking ENEC certificate				
Product Data					
Order product name	BSN 150/100 K302-A2-TS 230V 50Hz				

HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 150/100 K302-A2-TS 230V 50Hz	134 mm	113 mm	76 mm	65 mm	6.2 mm

