



HF-Selectalume II for TL5 lamps

HF-S 3/4 14 TL5 II 120V 50/60Hz

HF-Selectalume II TL5 is the most cost-effective, reliable and outstanding solution for fluorescent lamps. These ballasts are part of an overall high-efficiency lighting system that may help you or your customers to achieve any international or local energy code you need to comply with. HF-Selectalume II TL5 ballasts are the ideal choice for a broad range of new construction and retrofit applications within the commercial sector, including general surface mounting or office lighting, parking garages, warehouses, waterproof and other applications. The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.

Product data

| Operating and Electrical | |
|--|--------------------|
| Input Voltage | 120 V |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Earth Leakage Current (Max) | 0.5 mA |
| Inrush Current Width | 0.304 ms |
| Inrush Current Peak (Max) | 13 A |
| Number of Products on MCB (16A Type B) (Nom) | 30 |
| Wiring | |
| Connector Type Input Terminals | WAGO 744 connector |


| Connector Type Output Terminals | WAGO 744 connector [Suitable for manual wiring] |
|---------------------------------|---|
| Temperature | |
| Ambient temperature range | -20 °C to 55 °C |
| T-Case Lifetime (Nom) | 75 °C |
| T-Case Maximum (Max) | 75 °C |
| Mechanical and Housing | |
| Housing | L 280x40x21 |
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |
| Energy Efficiency Index | A2 BAT |

HF-Selectalume II for TL5 lamps

| | |
|--------------------|---------------------------------|
| Approval Marks | CE marking |
| Product Data | |
| Order product name | HF-S 3/4 14 TL5 II 120V 50/60Hz |
| Full product name | HF-S 3/4 14 TL5 II 120V 50/60Hz |
| Full product code | 871869653880700 |
| Order code | 913700768466 |

| | |
|---------------------------------|---------------|
| Material Nr. (12NC) | 913700768466 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696538807 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8718696538814 |

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|---------------------------------|--------|-------|--------|--------|-------|
| HF-S 3/4 14 TL5 II 120V 50/60Hz | 4.2 mm | 21 mm | 280 mm | 265 mm | 39 mm |

