



Core & Coil (71A) MH 175W - 450W

CORE & COIL HID MH BAL 175W M57 127/220V C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	M57-M107
Lamp Type	175/150W MH
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A55H0
Core Size	3 X 4 (2 LW)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	NA
Ignitor Temperature Rating	NA
Capacitor Value	10 MFD
Capacitor Catalog Number	7C100M40R
Capacitor Requirements	400V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.45 in
Capacitor Height	3.75 in
Automatic Restart	No

Operating and Electrical	
Input Voltage	127/220 V
Input Frequency	60 Hz
Inp. Current (Open Circuit)	1.65/1 A
Input Current (Starting)	1.11/0.64 A
Input Current (Short Circuit)	0.96-1.44/0.48-0.72 A
Secondary Short Circuit Current	1.5-1.9 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Nominal Open Circuit Voltage	305 V
Input Current (Operating) (Nom)	1.8/1.04 A A
Input Power (Nom)	210 W
Rated Lamp Watts	175/150 W


Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes

Core & Coil (71A) MH 175W - 450W

Max Ballast-Lamp Distance Remote Wiring Determined by AWG used	
Recommended Fuse Value	5/3 A
Approval and Application	
Open Circuit Voltage Test (Volts)	275-335 V
Approbation Marks	ULR CSA certificate NOM certificate RoHS Compliant
Temperature Marking	B/B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029B

Product Data	
Order product name	CORE & COIL HID MH BAL 175W M57 127/220V C&C
EAN/UPC - Product	781087034767
Order code	71A55H0500DML
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	913701105519
Net Weight (Piece)	3.403 kg

Dimensional drawing



MH BAL 175W M57 127/220V C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 175W M57 127/220V C&C	3.87 in	2.4 in	3.9 in	3.5 in	2.8 in	2.4 in

