

Core & Coil (71A) MH ~GT~ 450W

CORE & COIL HID MH BAL 1000W M47 5-TAP KIT (ALL CU)

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	M47
Lamp Type	1000W MH
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A6552CU
Core Size	4 1/4 x 6 (2 Coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	NA
Ignitor Temperature Rating	NA
Capacitor Value	24 MFD
Capacitor Catalog Number	MD2409000
Capacitor Requirements	480V
Capacitor Temperature Rating	90°C
Capacitor Diameter/Oval	1.75 in
Dimensions	
Capacitor Height	3.90 in
Automatic Restart	No


Operating and Electrical	
Input Voltage	120/208/240/277/480 V
Input Frequency	60 Hz
Input Current (Open Circuit)	5.16/4.3/3.09/2.61/1.6 A
Input Current (Starting)	6/2.82/3/2.3/1.53 A
Input Current (Short Circuit)	4.35-6.52/2.16-3.24/2.04-3.06/1.8-2.71/1-1.51 V
Secondary Short Circuit	4.97-6.08 A
Current	
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	426 V
Input Current (Nom)	9.05/5.6/4.7/4.07/2.36 A A
Input Power (Nom)	1080 W
Rated Lamp Power	1000 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded

Core & Coil (71A) MH ~GT~ 450W

Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance	Determined by AWG used
Remote Wiring	
Recommended Fuse Value	22/15/12/10/6 A
Approval and Application	
Open Circuit Voltage Test (Volts)	383-468 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	D/D/C/C/C
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)

UL Temperature Code	1029D
Product Data	
Order product name	CORE & COIL HID MH BAL 1000W M47 5-TAP KIT (ALL CU)
EAN/UPC - Product	781087098158
Order code	913701146201
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913701146201
Net Weight (Piece)	9.966 kg

Dimensional drawing



MH BAL 1000W M47 5-TAP KIT (ALL CU)

Product	C1	C2	A1	A2	A3	B1	B2
CORE & COIL HID MH BAL 1000W M47 5-TAP KIT (ALL CU)	4.70 in	3 in	6 in	5.4 in	4.4 in	4.3 in	3.9 in

