



# Core & Coil (71A) HPS 200W - 400W

## CORE & COIL HID HPS BAL 400W S51 230/400/480V C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information	
ANSI Code	S51-M169
Lamp Type	400W HPS
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A84Y3
Core Size	4 x 4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI501-H4
Ignitor Temperature Rating	105°C
Capacitor Value	55 MFD
Capacitor Catalog Number	7C550P24RA
Capacitor Requirements	240V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.80 in
Capacitor Height	3.70 in
Automatic Restart	No

Operating and Electrical	
Input Voltage	230/400/480 V
Input Frequency	60 Hz
Input Current (Open Circuit)	0.95/0.55/0.46 A
Input Current (Starting)	1.8/1/0.85 A
Input Current (Short Circuit)	1.44-2.16/0.81-1.21/0.68-1.02 A
Secondary Short Circuit Current	6.1-7.4 A
Constant Wattage Deviation	Within Trapezoid
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	190 V
Input Current (Nom)	2/1.2/1 A A
Input Power (Nom)	465 W
Rated Lamp Power	400 W


Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes

## Core & Coil (71A) HPS 200W - 400W

Max Ballast-Lamp Distance Remote	2'
<b>Wiring</b>	
Recommended Fuse Value	5/3/3 A
<b>Approval and Application</b>	
Open Circuit Voltage Test (Volts)	170-210 V
Approval Marks	ULR CSA certificate RoHS Compliant SASO Certificate
Temperature Marking	D/C/D
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)

UL Temperature Code	1029D
<b>Product Data</b>	
Order product name	CORE & COIL HID HPS BAL 400W S51 230/400/480V C&C
EAN/UPC - Product	781087130322
Order code	913701151202
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	3
Material Nr. (12NC)	913701151202
Net Weight (Piece)	7.154 kg

### Dimensional drawing



HPS BAL 400W S51 230/400/480V C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 400W S51 230/400/480V C&C	4.20 in	2.30 in	4.8 in	4.4 in	4.3 in	3.9 in

