



Centium T12HO

CENTIUM ELE BALLAST (2) F96T12/HO 120-277V

No matter what the conditions require, operating at a variety of line voltages between 120V to 480V, whether located in high ambient temperature environments (requiring a 90° C rating) or not, our family of Philips Advance Centium ballasts are ideal for a wide variety of applications.

Product data

General Information

Lamp type	F96T12/HO
Number of lamps	1/2 piece/unit
Ballast type	Electronic Fluorescent
Base model	ICN2S110SC
Suitable for outdoor use	Yes
Automatic restart	No

Operating and Electrical

Input voltage	120 to 277 V
Input frequency	50 to 60 Hz
Total harmonic distortion USA	10 %
Ignition method	Rapid Start
Crest factor (nom.)	1.7
Ignition time (nom.)	1 s
Ballast factor (nom.)	0.9
Power factor (nom.)	0.98
Input current (max.)	1.64 A
Input current (min.)	0.70 A
Input power (nom.)	191-186 W
Rated lamp power	110 W

Wiring

Colour input terminals	No terminals
Colour output terminals	No terminals
Wire strip length	0.50/0.375 mm
Lamp connection	Series
Wire length by colour	See data sheet
Wire gauge (nom.)	18AWG mm
Wire type	Solid
Remote wiring configuration allowed	Yes
Tandem wiring configuration allowed	Yes
Through-wiring configuration allowed	Yes
Max. ballast-lamp distance remote wiring	20'
Max. ballast-lamp distance tandem wiring	Red = 20'
Max. ballast-lamp distance through-wiring	Red = 20'
Connector type	No connector

Temperature

T-Case maximum (nom.)	70 °C
-----------------------	-------

Mechanical and Housing


Housing material	Metal
Housing	SC

Centium T12HO

Housing dimensions	9.5" x 1.7" x 1.18"
Approval and Application	
EMC immunity standard	FCC Non-Consumer
Approval marks	CSA certificate UL certificate CEC Listing Circle E logo CSA E DOE RoHS Compliant
Humming and noise level	A
UL recognised	No
Product Data	
Order product name	CENTIUM ELE BALLAST (2) F96T12/HO 120-277V

EAN/UPC – product	781087085288
Order code	913701212601
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	913701212601
Net weight (piece)	613.000 g

Dimensional drawing



Product	A1	A2	B1	C1
CENTIUM ELE BALLAST (2) F96T12/HO 120-277V	9.5 in	8.90 in	1.7 in	1.18 in

ELE BALLAST (2) F96T12/HO 120-277V

