



# Optanium Step Dim

## OPTANIUM ELE BALLAST (2) F54T5/HO 120-277V

Philips Advance Optanium ballasts with step-dim capability for T5 and T8 fluorescent lamps represent an affordable, energy-efficient, and versatile lighting solution designed to meet energy codes such as California’s Title 24 and ASHRAE 90.1-2010 that require end users to reduce lighting power consumption by 50%. Operating from any line voltage switching device, the ballast’s programmed-start circuitry provides extended lamp life in frequent switching applications like those associated with the use of occupancy sensors or motion detectors making this product the sustainable choice for many commercial applications.

### Product data

General Information	
Lamp Type	F54T5/HO
Number of Lamps	2 piece/unit
Ballast Type	Dimmable Fluorescent
Base Model	IOP2S54LSD
Suitable For Outdoor Use	Yes
Automatic Restart	Yes
Operating and Electrical	
Input Voltage	120 to 277 V
Input Frequency	50 to 60 Hz
Total Harmonic Distortion USA	10 %
Ignition Method	Programmed Start
Crestfactor (Nom)	1.7
Ignition Time (Nom)	1.5 s
Ballast Factor (Nom)	1.0
Power Factor (Nom)	0.98
Input Current (Max)	0.42 A
Input Current (Min)	0.98 A

Input Power (Nom)	54-54 W
Rated Lamp Power	54 W
Wiring	
Color Input Terminals	Black and White
Color Output Terminals	RED, YEL & BLU
Wire Striplength	0.375 mm
Lamp Connection	Series
Wire Length by Color	No wires
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	Yes
Through Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	7'
Max Ballast-Lamp Distance Tandem Wiring	Any = 7'
Max Ballast-Lamp Distance Through Wiring	Any = 7'
Connector Type	Poke-In

## Optanium Step Dim

Temperature	
T-Case Maximum (Nom)	70 °C

Mechanical and Housing	
Housing Material	Metal
Housing	D
Housing Dimensions	16.7" x 1.18" x 1.0"


Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate CEC Listing CEE Rated CSA E NEMA Premium RoHS Compliant
Hum And Noise Level	A

UL Recognized	No
---------------	----

Product Data	
Order product name	OPTANIUM ELE BALLAST (2) F54T5/HO 120-277V
EAN/UPC - Product	781087133873
Order code	913701259902
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	913701259902
Net Weight (Piece)	531.000 g

### Dimensional drawing



ELE BALLAST (2) F54T5/HO 120-277V

Product	A1	B1	C1
OPTANIUM IOP2S54LSD35M	16.7 in	1.18 in	1.0 in

