



Mark 7 0-10V

MARK 7 0-10V ELE DIMMING BALLAST (2) F32T8 120-277V

The Mark 7 0–10V series of dimmable electronic ballasts offer maximum versatility by incorporating separate control leads for use with a wide array of controllers, including occupancy sensors, daylight harvesting controls, and building management systems from more than 40 manufacturers. When paired with linear fluorescent and 4-pin compact fluorescent lamps, these ballasts optimize the benefits of such popular sustainable lighting techniques as daylight harvesting, occupancy sensing, and load shedding to satisfy the need for an affordable, flexible and versatile controllable lighting solution.

Product data

General Information				
Lamp Type	F32T8			
Number of Lamps	2 piece/unit			
Ballast Type	Dimmable Fluorescent			
Base Model	IZT2PSP32SC			
Suitable For Outdoor Use	Yes			
Automatic Restart	Yes			
Operating and Electrical				
Input Voltage	120 to 277 V			
Input Frequency	50 to 60 Hz			
Total Harmonic Distortion USA	10 %			
Ignition Method	Programmed Start			
Crestfactor (Nom)	1.6			
Ignition Time (Nom)	1.5 s			
Ballast Factor (Max)	1.00			
Ballast Factor (Min)	0.05			
Power Factor (Nom)	0.99			

Input Current (Max)	0.54 A		
Input Current (Min)	0.23 A		
Input Current (Nom)	- A		
Input Power (Max)	67 W		
Input Power (Min)	11 W		
Rated Lamp Power	32 W		
Wiring			
Color Input Terminals	No terminals		
Color Output Terminals	No terminals		
Wire Striplength	0.50/0.375 mm		
Control Wire Gauge	18AWG		
Lamp Connection	Series		
Wire Length by Color	See Data Sheet		
Wire Gauge (Nom)	18AWG mm		
Wire Type	Solid		
Remote Wiring Configuration Allowed	Yes		
Tandem Wiring Configuration Allowed	Yes		

Mark 7 0-10V

Yes				
6'				
g Any = 6'				
Max Ballast-Lamp Distance Through Wiring Any = 6'				
No connector				
70 °C				
Metal				
Metal SC				
SC				
SC				

Compliant

CSA certificate UL certificate CEC Listing CEE Rated CSA E NEMA Premium RoHS

Hum And Noise Level	А		
UL Recognized	No		
Product Data			
Order product name	MARK 7 0-10V ELE DIMMING BALLAST (2)		
	F32T8 120-277V		
EAN/UPC - Product	781087134849		
Order code	913701260902		
Numerator - Quantity Per Pack	1		
Numerator - Packs per outer box	20		
Material Nr. (12NC)	913701260902		
Net Weight (Piece)	441.000 g		

Dimensional drawing

Approval Marks



Product	A1	A2	B1	C1
MARK 7 0-10V ELE DIMMING BALLAST (2)	9.50 in	8.90 in	1.70 in	1.18 in
F32T8 120-277V				





© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.