




BPL EM ballasts for CFL, PLT, PLS and PLC lamps (India)

BPL 018 X261


Range of copper ballasts produced with a high level of accuracy on current settings to ensure optimum operation of compact fluorescent lamps. Designed for compact fluorescent lamps to be operated on 240 V-50 Hz mains supply.

Product data

Operating and Electrical		Order product name	
Input Voltage	240 V	BPL 018 X261	
Line Frequency	50 Hz	Order code	
Input Frequency	50 Hz	913702235212	
Wiring		Numerator - Quantity Per Pack	
Connector Type	Screw	1	
Approval and Application		Numerator - Packs per outer box	
Approval Marks	CE marking	20	
Product Data		Material Nr. (12NC)	
Full product code	871150088433600	913702235212	
		Full product name	
		BPL 018 X261	
		EAN/UPC - Case	
		8727900067248	
		EAN/UPC - Product/Case	
		8711500884336	

BPL EM ballasts for CFL, PLT, PLS and PLC lamps (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
BPL 018 X261	4.2 mm	28.0 mm	87.0 mm	70.0 mm	39.0 mm

