



Sumo Electronic ballast for TL5/TL-D lamps (India)

Sumo ultra 136

Compact, lightweight, high-frequency electronic ballasts for TL-D/TL5 fluorescent lamps


Product data

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Wiring	
Connector Type Input Terminals	- [Not specified]
Connector Type Output Terminals	- [Not specified]
Temperature	
Ambient temperature range	0 °C to 50 °C
T-Case Maximum (Max)	65 °C
Approval and Application	
Energy Efficiency Index	Not specified

Safety Standard	- [Not specified]
Product Data	
Order product name	Sumo ultra 136
Full product name	Sumo ultra 136
Full product code	871829118532100
Order code	913702241410
Material Nr. (12NC)	913702241410
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291185321
Numerator - Packs per outer box	30
EAN/UPC - Case	8718291185338

Sumo Electronic ballast for TL5/TL-D lamps (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
Sumo ultra 136	4.0 mm	27.0 mm	136.0 mm	130.0 mm	40.0 mm

