



# Dynalite Phase-Cut Dimmers

## DLE1210

Philips Dynalite supports a wide selection of dimmer units that are compatible with most lamp types. By selecting the right dimmer for the different lamp types, an unlimited number of combinations of dimmer units can be chosen to work together in one project. Utilizing the very latest in microprocessor technology, every Dynalite dimmer has many built-in dedicated features for the lighting control industry. Industry-leading 16-bit fading resolution allows ultra-smooth dimming in projects where this is critical for flicker-free scene changes. The dimmers are capable of fading from one scene to another over a period ranging from one second to 23 hours, triggered from a single network message. This allows simpler programming and a smooth transition from one scene to the next – a feature that is perfect for daylight harvesting in projects requiring energy management.

### Product data

| General Information |   |                                 |                 |
|---------------------|---|---------------------------------|-----------------|
| Remarks             | Please download the Lighting - Product Data Sheet for more information and ordering options | Full product code               | 871016350554100 |
| CE mark             | CE mark   | Order code                      | 50554100        |
| EU RoHS compliant   | Yes   | Material Nr. (12NC)             | 913703012009    |
| Product Data        |   | Numerator - Quantity Per Pack   | 1               |
| Order product name  | DLE1210   | EAN/UPC - Product/Case          | 8710163505541   |
| Full product name   | DLE1210   | Numerator - Packs per outer box | 1               |
|                     |   | EAN/UPC - Case                  | 8710163505558   |