



Dynalite Phase-Cut Dimmers

DLE1220GL

Philips Dynalite supports a wide selection of dimmer units that are compatible with most lamp types. By selecting the right dimmer for the different lamp types, an unlimited number of combinations of dimmer units can be chosen to work together in one project. Utilizing the very latest in microprocessor technology, every Dynalite dimmer has many built-in dedicated features for the lighting control industry. Industry-leading 16-bit fading resolution allows ultra-smooth dimming in projects where this is critical for flicker-free scene changes. The dimmers are capable of fading from one scene to another over a period ranging from one second to 23 hours, triggered from a single network message. This allows simpler programming and a smooth transition from one scene to the next – a feature that is perfect for daylight harvesting in projects requiring energy management.

Product data

General Information			
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product name	DLE1220GL
CE mark	CE mark	Full product code	871016350572500
EU RoHS compliant	Yes	Order code	913703016009
Temperature		Material Nr. (12NC)	913703016009
Ambient temperature range	0 to +40 °C	Numerator - Quantity Per Pack	1
Product Data		EAN/UPC - Product/Case	8710163505725
Order product name	DLE1220GL	Numerator - Packs per outer box	1
		EAN/UPC - Case	8710163505732

Dynalite Phase-Cut Dimmers

Dimensional drawing

