



Dynalite Phase-Cut Dimmers

DTE1210

Leading Edge Dimmer Controllers are ideal for lighting circuits with resistive and inductive properties, including mains voltage incandescent fittings, neon and low voltage lamps with a compatible electronic transformer. Available in both DIN-rail and wall box configuration, Dynalite supports a vast range of leading edge dimmer controllers with a variety of circuit numbers and sizes to work individually or part of a system, fitting any project requirement. Wall box dimmer controllers have been engineered to achieve rise times of over 100µS producing reduced filament sing, reduced supply voltage noise, resulting in extended lamp life. The dimmers are engineered to be compatible with electronic transformers, requiring less de-rating, therefore allowing full capacity of channel to be utilized.

Product data

General Information			
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product name	DTE1210
CE mark	CE mark	Full product code	871016350586200
EU RoHS compliant	Yes	Order code	913703022009
Temperature		Material Nr. (12NC)	913703022009
Ambient temperature range	0 to +40 °C	Numerator - Quantity Per Pack	1
Product Data		EAN/UPC - Product/Case	8710163505862
Order product name	DTE1210	Numerator - Packs per outer box	1
		EAN/UPC - Case	8710163505879

Dynalite Phase-Cut Dimmers

Dimensional drawing

