



Dynalite Multipurpose Controllers

DMC810GL

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Product data

General Information	
Remarks	Please download the Lighting – Product Data Sheet for more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes
Temperature	
Ambient temperature range	0 to +40 °C
Product Data	
Full EOC	871016350632600

Order product name	DMC810GL
Order code	50632600
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12 NC)	913703028009
Full product name	DMC810GL
EAN/UPC – Case	8710163506333
EAN/UPC – Product/Case	8710163506326

Dynalite Multipurpose Controllers

Dimensional drawing

