



Dynalite Relay Controllers

DDRC810DT-GL

As one of the most popular forms of lighting control, relay controllers can have the greatest impact in terms of energy management and lighting control. Available in both DIN-rail and wall-box configurations, this Dynalite solution enables a vast range of relay controllers with a variety of circuit numbers and sizes to work individually or as part of a system, thus fulfilling any project requirement. Each device can store over 170 presets, allowing the recall of complex switching logic from simple network messages. As the required preset scenarios are stored within each relay device, the commissioning process and network messages are simplified.

Product data

General Information		Full product name	DDRC810DT-GL
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product code	871869600688700
CE mark	CE mark	Order code	913703035209
EU RoHS compliant	Yes	Material Nr. (12NC)	913703035209
Temperature		Numerator - Quantity Per Pack	1
Ambient temperature range	0 to +50 °C	EAN/UPC - Product/Case	8718696006887
Product Data		Numerator - Packs per outer box	1
Order product name	DDRC810DT-GL	EAN/UPC - Case	8718696014387

Dynalite Relay Controllers

Dimensional drawing

