



# Dynalite Relay Controllers

## DDRC420FR V1

As one of the most popular forms of lighting control, relay controllers can have the greatest impact in terms of energy management and lighting control. Available in both DIN-rail and wall-box configurations, this Dynalite solution enables a vast range of relay controllers with a variety of circuit numbers and sizes to work individually or as part of a system, thus fulfilling any project requirement. Each device can store over 170 presets, allowing the recall of complex switching logic from simple network messages. As the required preset scenarios are stored within each relay device, the commissioning process and network messages are simplified.

### Product data

<b>General Information</b>		<b>Order product name</b>	DDRC420FR V1
<b>Remarks</b>	Please download the Lighting - Product Data Sheet for more information and ordering options	<b>Order code</b>	913703051009
<b>CE mark</b>	CE mark	<b>Numerator - Quantity Per Pack</b>	1
<b>EU RoHS compliant</b>	Yes	<b>Numerator - Packs per outer box</b>	1
<b>Temperature</b>		<b>Material Nr. (12NC)</b>	913703051009
<b>Ambient temperature range</b>	0 to +50 °C	<b>Full product name</b>	DDRC420FR V1
<b>Product Data</b>		<b>EAN/UPC - Case</b>	8710163506913
<b>Full product code</b>	871016350690600	<b>EAN/UPC - Product/Case</b>	8710163506906