



# Dynalite LED PWM Controllers

## DDLEDC605GL

Capable of directly driving LED fittings, the Dynalite LED Dimmers use Pulse Width Modulation (PWM) technology to great effect. Perfectly suited to Red, Green, Blue (RGB) color changing applications, chase sequencing or provision of elegant scene settings. The Dynalite LED drivers come in a range of configurations to meet the compatibility requirements of many of the available LED fittings. Each device is ready to receive native DMX allowing them to be used in color mixing or chase sequence applications.

### Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes
Temperature	
Ambient temperature range	0 to +40 °C
Product Data	
Order product name	DDLEDC605GL

Full product name	DDLEDC605GL
Full product code	871016351646200
Order code	913703061209
Material Nr. (12NC)	913703061209
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163516462
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163516479

# Dynalite LED PWM Controllers

## Dimensional drawing

