



# ET-S transformer

## ET-S 105

High-frequency electronic transformer (60, 105 and 150 W versions available), operation with 12 V halogen lamps


### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	0.16 ms
Wiring	
Connector Type Input Terminals	Screw
Connector Type Output Terminals	Screw
Cable Length From Device to Lamp	1.5 m
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Max)	85 °C

Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	ET-S 105
Full product name	ET-S 105
Full product code	872790087626000
Order code	913710031660
Material Nr. (12NC)	913710031660
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900876260
Numerator - Packs per outer box	50
EAN/UPC - Case	8727900876277

ET-S transformer

Dimensional drawing



Product	D1	C1	A1	B1
ET-S 105	4.2 mm	33.5 mm	112.0 mm	54.0 mm

