



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 250L 300I

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking CCC certificate
Product Data	
Order product name	BSN 250L 300I

Full product name	BSN 250L 300I
Full product code	871016303091330
Order code	913710100250
Material Nr. (12NC)	913710100250
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163148137
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163031903

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 250L 300I	6.2 mm	64.5 mm	150.0 mm	135 mm	75.5 mm

