

# HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

## BSN 400L 304I

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


### Product data

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	BSN 400L 304I

Full product name	BSN 400L 304I
Full product code	871016303208500
Order code	913710101150
Material Nr. (12NC)	913710101150
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163148236
Numerator - Packs per outer box	4
EAN/UPC - Case	8710163032085

# HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 400L 304I	6.2 mm	82 mm	165.0 mm	150 mm	96.5 mm

