



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 400L 304I


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name		BSN 400L 304I
Input Voltage	240 V	Full product code		871016303208500
Line Frequency	50 Hz	Order code		913710101150
Input Frequency	50 Hz	Material Nr. (12NC)		913710101150
		Numerator - Quantity Per Pack		1
		EAN/UPC - Product/Case		8710163148236
		Numerator - Packs per outer box		4
		EAN/UPC - Case		8710163032085
Approval and Application				
Approval Marks	CE marking			
Product Data				
Order product name	BSN 400L 304I			

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 400L 304I	6.2 mm	82 mm	165.0 mm	150 mm	96.5 mm

