

# HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

## BSN 400L 304I


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

### Product data

General Information		Temperature	
Application Code	L304 I	T-Winding (Max)	130 °C
		Delta-T Normal Conditions	75 °C
Operating and Electrical		Approval and Application	
Input Voltage	240 V	Approval Marks	CE marking
Input Frequency	50 Hz		
Power Factor 100% Load (Min)	0.85	Product Data	
Mains Voltage Performance (AC)	-8% - +6%	Full product code	871016303208500
Mains Voltage Safety (AC)	-10% - +10%	Order product name	BSN 400L 304I
Input Current with PF Correction	2.4 A	EAN/UPC - Product	8710163148236
Input Current without PF Correction	4.45 A	Order code	913710101150
Power Factor without PF Compensation (Nom)	0.40	Numerator - Quantity Per Pack	1
Power Losses (Nom)	33.0 W	Numerator - Packs per outer box	4
Wiring		Material Nr. (12NC)	913710101150
Connector Type	Screw	Net Weight (Piece)	4.500 kg
System characteristics			
Rated Ballast-Lamp Power	400 W		

## HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

### Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 400L 304I	6.2 mm	82 mm	165.0 mm	150 mm	96.5 mm

BSN 400 L304 I

