



HID-Basic ballasts for HPL and HPI(PLUS) lamps

BHL 250L 204

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.


Product data

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	BHL 250L 204

Full product name	BHL 250L 204
Full product code	871016303210800
Order code	913710101250
Material Nr. (12NC)	913710101250
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163148250
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163032108

HID-Basic ballasts for HPL and HPI(PLUS) lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 250L 204	6.2 mm	64.5 mm	125.0 mm	110.0 mm	75.5 mm

