



HID-Basic ballasts for HPL and HPI(PLUS) lamps

BHL 250L 201

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.


Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Input Frequency	60 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	BHL 250L 201

Full product name	BHL 250L 201
Full product code	871016303468300
Order code	913710101816
Material Nr. (12NC)	913710101816
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163034683
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696431627

HID-Basic ballasts for HPL and HPI(PLUS) lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 250L 201	6.2 mm	64.5 mm	125.0 mm	110.0 mm	75.5 mm

