



# HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

## BSN 250L 301I TS


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BSN 250L 301I TS
Input Voltage	230 V	Full product code	871016303120030	
Line Frequency	50 Hz	Order code	913710102143	
Input Frequency	50 Hz	Material Nr. (12NC)	913710102143	
<b>Wiring</b>		Numerator - Quantity Per Pack	1	
Connector Type	Screw	EAN/UPC - Product/Case	8710163148281	
<b>Product Data</b>		Numerator - Packs per outer box	6	
Order product name	BSN 250L 301I TS	EAN/UPC - Case	8710163032191	

# HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 250L 3011 TS	6.3 mm	64.5 mm	150.0 mm	135.0 mm	72.5 mm

