




HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 250 L302I


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name		BSN 250 L302I	
Input Voltage	230 V	Full product code		871016303131630	
Line Frequency	50 Hz	Order code		03131630	
Input Frequency	50 Hz	Material Nr. (12NC)		913710102850	
Wiring		Numerator - Quantity Per Pack		1	
Connector Type	Screw	EAN/UPC - Product/Case		8710163148366	
Product Data		Numerator - Packs per outer box		6	
Order product name	BSN 250L 302I	EAN/UPC - Case		8710163032306	

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 250L 302I	6.3 mm	64.5 mm	150.0 mm	129.0 mm	72.5 mm

