



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN400L301I 220V 60HZ

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	
Input Voltage	220 V	Full product code	BSN400L301I 220V 60HZ
Line Frequency	60 Hz	Order code	871016303473730
Input Frequency	60 Hz	Material Nr. (12NC)	03473730
Wiring		Numerator - Quantity Per Pack	913710102950
Connector Type	Screw	EAN/UPC - Product/Case	1
Approval and Application		Numerator - Packs per outer box	8710163148830
Approval Marks	CE marking	EAN/UPC - Case	4
Product Data			
Order product name	BSN 400L 301I		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 400L 301I	6.2 mm	82 mm	165.0 mm	150 mm	96.5 mm

