

# HID-Basic Semi-Parallel ballasts for MHN/CDM lamps

## BMH 35L 302I TS


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for metal-halide and CDM lamps.

### Product data

<b>Operating and Electrical</b>		<b>Order product name</b>	
Input Voltage	230 V	Order code	913710103150
Line Frequency	50 Hz	Numerator - Quantity Per Pack	1
Input Frequency	50 Hz	Numerator - Packs per outer box	6
<b>Wiring</b>		Material Nr. (12NC)	913710103150
Connector Type	Screw	Full product name	BMH 35L 302I TS
<b>Approval and Application</b>		EAN/UPC - Case	8710163032368
Approval Marks	CE marking CCC certificate	EAN/UPC - Product/Case	8710163148410
<b>Product Data</b>			
Full product code	871016303137830		

# HID-Basic Semi-Parallel ballasts for MHN/CDM lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BMH 35L 302I TS	6.2 mm	51.5 mm	117.0 mm	102.0 mm	57.1 mm

