



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 70L 3001


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	BSN 70L 3001
Input Voltage	220 V	Full product code	871016303260300
Line Frequency	50 Hz	Order code	913710104550
Input Frequency	50 Hz	Material Nr. (12NC)	913710104550
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8710163148502
		Numerator - Packs per outer box	6
		EAN/UPC - Case	8710163032603
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking		
Product Data			
Order product name	BSN 70L 3001		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 70L 300I	6.2 mm	51.5 mm	117.0 mm	102 mm	57.1 mm

